

## CPL4153 (Chemical Absorbent Big Pillow)

- Applicable for most acids, alkalis, corrosives, chemicals and unknown liquids
- Ideal for mass liquids leakage containment to avoid spill spreading
- Pillows are easy to place in hard-to-reach areas — use under shelves and leaky hydraulic hoses or wedge in corners cramped for space
- Has equal sump capacity as 42 pcs chemical absorbent pads
- Compact design for absorbency capacity enlargement to catch up persistent drips and leaks
- Plastic packaging will not be ruined by water and self-extinguish with fire
- Velcro seal eliminates sealing tape and realizes fast open-up
- Optional fluorescent sticker to the outer packaging for fast eye-catching in emergencies
- Absorbent in high fiber construction leave no fiber residue



## Technical Data Sheet

Brand	UPQUARK
Model	CPL4153
Fluid absorbed	Most Hazmat chemical liquids
Dimensions(inch)	41cm x 53cm x 15cm(16 x 21 x 6")
Color	Yellow
Skin/Outer Mesh	Abrasion resistant spun bond
Filler	Polypropylene
Net Weight kg (pound)	5.1 (11)
Absorbency per Box liter(gallon)	51 (13)
Absorbency per Pillow liter(gallon)	17 (4.3)
Sold as	3 Pillows per Plastic Box
Meets Regulations	29 CFR 1910.22(a)(2)

Note:

1. Pls refer to local hazardous waste disposal methods after product application. Incineration is not recommended. Self-incineration may cause fire or produce toxic and harmful gases due to the decomposition of materials and adsorbed liquids.
2. PPE is compulsory for on-site personnel matching the hazard level of leaked chemical liquids.
3. Mixing of different saturated absorbent is prohibited in chemical-proof garbage bag.
4. Move and clean absorbed liquid asap.



**Technical Service:**  
[technicalsupport@upquarksafety.com](mailto:technicalsupport@upquarksafety.com)