

CPL2046 (Chemical Absorbent Pillow)

- Applicable for most acids, alkalis, corrosives, chemicals and unknown liquids
- Ideal for mass liquids leakage containment to avoid spill spreading
- Pillows are easy to place in hard-to-reach areas — use under shelves and leaky hydraulic hoses or wedge in corners cramped for space
- Its design to enlarge spill contacting area to realize liquid quick soak up
- Compact design for absorbency capacity enlargement to catch up persistent drips and leaks
- Plastic packaging will not be ruined by water and self-extinguish with fire
- Velcro seal eliminates sealing tape and realizes fast open-up
- Optional Fluorescent sticker to the outer packaging for fast eye-catching in emergencies
- Absorbent in high fiber construction leave no fiber residue



Technical Data Sheet

Brand	UPQUARK
Model	CPL2046
Fluid absorbed	Most Hazmat chemical liquids
Dimensions(inch)	20cm x 46cm(8 x 18")
Color	Yellow
Skin/Outer Mesh	Abrasion resistant spun bond
Filler	Polypropylene
Net Weight kg (pound)	4.4 (9.7)
Absorbency per Box liter(gallon)	44 (12)
Absorbency per Pillow liter(gallon)	2.2 (0.6)
Sold as	20 Pillows per Plastic Box
Meets Regulations	29 CFR 1910.22(a)(2)

Note:

1. Pls refer to local hazardous waste disposal methods after product application. Incineration is not recommended. Self-incineration may cause fire or produce toxic and harmful gases due to the decomposition of materials and adsorbed liquids.
2. PPE is compulsory for on-site personnel matching the hazard level of leaked chemical liquids.
3. Mixing of different saturated absorbent is prohibited in chemical-proof garbage bag.
4. Move and clean absorbed liquid asap.



Technical Service:
technicalsupport@upquarksafety.com